

## 1 1/2" Grab Bars – Concealed Screw

### AL Numbers:

- ❑ **AL-77509-12, AL-77510-12 – 12" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-16, AL-77510-16 – 16" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-18, AL-77510-18 – 18" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-24, AL-77510-24 – 24" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-30, AL-77510-30 – 30" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-32, AL-77510-32 – 32" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-36, AL-77510-36 – 36" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-42, AL-77510-42 – 42" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting
- ❑ **AL-77509-48, AL-77510-48 – 48" Grab Bar**  
Stainless or White Finish  
1 1/2" Bar, Concealed Screw Mounting


### Materials:

1 1/2" **grab bar** rods are formed from type 304 stainless steel tubing.  
12" – 42" length is 20 gauge  
48" length is 18 gauge

### Compliance:

- ADA, ANSI, ASTM, CSA
- Tested to 500 lbs. pull

### Dimensions:



### Installation Instructions:

1. Position unit on wall in desired location.
2. Mark mounting holes.
3. Drill starter holes.
4. Mount unit on wall using 2" screws (provided).
5. Snap flange covers into place.

Note: SecureMount Anchors are recommended for use in non-stud (hollow-wall) applications per installation instructions.